
## INSTALLATION INSTRUCTION



## PRODUCT FEATURE

- Compact design enables an easy introduction in a tank.
- Low amperage draw DC-12V / 24V available
- Designed for intermittent use and fully submersible only. Max. continuous operation should not exceed 15 minutes.
- Wide variety of uses including emptying, filling and transferring of liquid containing no solid matter.

## NOTES

- Do not run the pump dry.
- Do not use the pump in water temperature above 60°C (140°F)
- Max. continuous operation should not exceed 15 minutes.
- Check that the polarity is correct.

