

## Moplen EP300K

### Polypropylene, Impact Copolymer

#### Product Description

Moplen EP300K is a low fluidity heterophasic copolymer, suitable for injection moulding applications.

The product exhibits very high impact even at low temperature combined with a good stiffness.

Moplen EP300K is typically used in houseware items and in crates.

#### Product Characteristics

<b>Status</b>	Commercial: Active
<b>Test Method used</b>	ISO
<b>Availability</b>	Europe, Africa-Middle East
<b>Processing Method</b>	Injection Molding, Extrusion Thermoforming
<b>Features</b>	High Impact Resistance , Good Stiffness
<b>Typical Customer Applications</b>	Crates, Caps & Closures, Housewares

Typical Properties	Method	Value Unit
<b>Physical</b>		
Density	ISO 1183	0.9 g/cm <sup>3</sup>
Melt flow rate (MFR) (230°C/2.16Kg)	ISO 1133	4 g/10 min
Melt volume flow rate (230°C/2.16Kg)	ISO 1133	5.4 cm <sup>3</sup> /10min
<b>Mechanical</b>		
Tensile Modulus	ISO 527-1, -2	1200 MPa
Tensile Stress at Yield	ISO 527-1, -2	27 MPa
Tensile Strain at Break	ISO 527-1, -2	>50 %
Tensile Strain at Yield	ISO 527-1, -2	7 %
<b>Impact</b>		
Charpy unnotched impact strength (23 °C, Type 1, Edgewise)	ISO 179	No Break kJ/m <sup>2</sup>
(0 °C, Type 1, Edgewise)		140 kJ/m <sup>2</sup>
(-20 °C, Type 1, Edgewise)		80.0 kJ/m <sup>2</sup>
Charpy notched impact strength (23 °C, Type 1, Edgewise, Notch A)	ISO 179	10.5 kJ/m <sup>2</sup>
(0 °C, Type 1, Edgewise, Notch A)		5.5 kJ/m <sup>2</sup>
(-20 °C, Type 1, Edgewise, Notch A)		4 kJ/m <sup>2</sup>
<b>Hardness</b>		
Ball indentation hardness (H 358/30)	ISO 2039-1	53 MPa
<b>Thermal</b>		
Heat deflection temperature B (0.45 MPa) Unannealed	ISO 75B-1, -2	75 °C
Vicat softening temperature (A50 (50°C/h 10N))	ISO 306	150 °C
(B50 (50°C/h 50N))		71 °C

## Notes

Typical properties; not to be construed as specifications.

## Further Information

---

*Moplen EP300K*

Conveying: Conveying equipment should be designed to prevent production and accumulation of fines and dust particles that are contained in polymer resins. These particles can under certain conditions pose an explosion hazard. We recommend the conveying system used is equipped with adequate filters, is operated and maintained that no leak develops and adequate grounding exists at all times.

### Health and Safety:

The resin is manufactured to the highest standards but, special requirements apply to certain applications such as food end-use contact and direct medical use. For specific information on regulatory compliance contact your local representative.

Workers should be protected from the possibility of skin or eye contact with molten polymer. Safety glasses are suggested as a minimal precaution to prevent mechanical or thermal injury to the eyes.

Molten polymer may be degraded if it is exposed to air during any of the processing and off-line operations. The products of degradation have an unpleasant odour. In higher concentrations they may cause irritation of the mucus membranes. Fabrication areas should be ventilated to carry away fumes or vapours. Legislation on the control of emissions and pollution prevention must be observed. If the principles of sound manufacturing practice are adhered to and the place of work is well ventilated, no health hazards are involved in processing the resin.

The resin will burn when supplied with excess heat and oxygen. It should be handled and stored away from contact with direct flames and/or ignition sources. In burning the resin contributes high heat and may generate a dense black smoke. Starting fires can be extinguished by water, developed fires should be extinguished by heavy foams forming an aqueous or polymeric film. For further information about safety in handling and processing please refer to the Material Safety Data Sheet.

### Storage:

The resin is packed in 25 kg bags or in bulk containers protecting it from contamination. If it is stored under adverse conditions, i. e. if there are large fluctuations in ambient temperature and the atmospheric humidity is high, moisture may condense inside the packaging. Under these circumstances, it is recommended to dry the resin before use. Unfavourable storage conditions may also intensify the resin's slight characteristic odour.

The resin is subjected to degradation by ultra-violet radiations or by high storage temperatures. Therefore the resin must be protected from direct sunlight, temperatures above 40°C and high atmospheric humidity during storage. The resin can be stored over a period of more than 6 months without significant changes in the specified properties, appropriate storage conditions provided. Higher storage temperatures reduce the storage time.

The information submitted is based on our current knowledge and experience. In view of the many factors that may affect processing and application, these data do not relieve processors of the responsibility of carrying out their own tests and experiments; neither do they imply any legally binding assurance of certain properties or of suitability for a specific purpose. The data do not relieve the customer from his obligation to control the resin upon arrival and to complain about faults. It is the responsibility of those to whom we supply our products to ensure that any proprietary rights and existing laws and legislation are observed.

© LyondellBasell Industries Holdings, B.V. 2010

For the contact details of the LyondellBasell company selling this product in your country, please visit <http://www.lyondellbasell.com/>.

Before using a product sold by one of the LyondellBasell family of companies, users should make their own independent determination that the product is suitable for the intended use and can be used safely and legally. SELLER MAKES NO WARRANTY; EXPRESS OR IMPLIED (INCLUDING ANY WARRANTY OF

MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE) OTHER THAN AS SEPARATELY AGREED BETWEEN THE PARTIES IN WRITING. This product(s) may not be used in the manufacture of any US FDA Class III Medical Device or Health Canada Class IV Medical Device and may not be used in the manufacture of any US FDA Class II Medical Device or Health Canada Class II or Class III Medical Device without the prior written approval by Seller of each specific product or application.

Users should review the applicable Material Safety Data Sheet before handling the product.

*Adflex, Adstif, Adsyl, Akoafloor, Akoalit, Alastian, Alathon, Alkylate, Aquamarine, Aquathene, Arconate, Arcopure, Arcosolv, Arctic Plus, Arctic Shield, Avant, Catalloy, Clyrell, CRP, Crystex, Dexflex, Duopac, Duoprime, Duotreat, Filmex, Flexathene, Get in touch with, Glacido, Glidox, Glidsol, Hifax, Histif, Hostacom, Hostalen PP, Hostalen ACP, Ideal, Indure, Integrate, Koattro, LIPP, Lucalen, Luflexen, Lupocomp, Lupolen, Lupolex, Luposim, Lupostress, Lupotech, Metocene, Microthene, Moplen, MPDIOL, Navacet, Nerolex, Nexprene, Petrothene, Plexar, Polymeg, Pristene, Prodflex, Pro-Fax, Punctilious, Purell, SAA 100, SAA 101, Sequel, Softell, Spherilene, Spheripol, Spherizone, Starflex, Stretchene, Superflex, TBAC, Tebol, Tetralol, T-Hydro, Topyl, Trans4m, Tufflo, Ultrathene, Vacido, Valtec, and Winsense* are trademarks owned and/or used by LyondellBasell group companies.

*Akoafloor, Akoalit, Alastian, Alathon, Aquamarine, Arconate, Arcopure, Arcosolv, Arctic Plus, Arctic Shield, Avant, Clyrell, CRP, Crystex, Dexflex, Duopac, Duoprime, Filmex, Flexathene, Glidox, Glidsol, Hifax, Hostacom, Hostalen, Ideal, Indure, Integrate, Koattro, Lucalen, Lupolen, Microthene, Moplen, MPDIOL, Nexprene, Petrothene, Plexar, Polymeg, Pristene, Pro-Fax, Punctilious, Purell, Sequel, Spheripol, Spherizone, Softell, Starflex, Tebol, Tetralol, T-Hydro, Topyl, Tufflo, Ultrathene, and Winsense* are registered in the U.S. Patent and Trademark Office.

Release Date: 03 Aug 2009